

DIAMOND 8111

A very popular textile gloves with ceramic coating and anti-shock filling. The high durability is completed by compliance with EN 659 even after a series of 40 washing cycles. Five different cuff variants and three colors for optimum adaptation to the firefighting jacket.



DIAMOND Flexi Navy Blue



DIAMOND Easy Beige



DIAMOND Evo Red



DIAMOND Short Navy Blue



DIAMOND Long Beige

PRODUCT DESCRIPTION

DIAMOND Flexi	■ Navy Blue	8111-01
DIAMOND Evo	■ Navy Blue	8111-02
DIAMOND Easy	■ Navy Blue	8111-03
DIAMOND Long	■ Navy Blue	8111-04
DIAMOND Short	■ Navy Blue	8111-05
DIAMOND Flexi	■ Beige	8111-11
DIAMOND Evo	■ Beige	8111-12
DIAMOND Easy	■ Beige	8111-13
DIAMOND Long	■ Beige	8111-14
DIAMOND Short	■ Beige	8111-15
DIAMOND Flexi	■ Red	8111-21
DIAMOND Evo	■ Red	8111-22
DIAMOND Easy	■ Red	8111-23
DIAMOND Long	■ Red	8111-24
DIAMOND Short	■ Red	8111-25

UPPER MATERIAL:

- **Back:** Nomex[®] fabric with hydrophobic and oleophobic treatment, reinforced with ceramic coating in exposed areas.
- **Palm:** Meta-aramid / Para-aramid knit with silicone coating.

REINFORCEMENT:

- Back knuckles are protected against impact by impact-resistant foam placed in the inner layers of the glove. Ceramic coating increases abrasion resistance on both the fingers and the back reinforcement.
- Ceramic coating: The fingertips are no longer protected by reinforcements but by ceramic coating, making this area more flexible without reducing protection. This technology reduces weight and increases glove sensitivity.

INTERMEDIATE LAYERS:

1. Insulation layer – Recycled aramid non-woven fabric.
2. Membrane – FR Porelle[®] membrane.

DuPont[™], Kevlar[®] and Nomex[®] are trademarks or registered trademarks of E.I. du Pont de Nemours and Company.

DIAMOND 8111

LINING:

- Aramid lining.

CUFFS:

- **Flexi** – Cuff made of flame retardant fabrics with stable internal elastic.
- **Evo** – Nomex cuff with flexible barrier made of non-flammable fabrics.
- **Easy** – Cuff made of Nomex fabric.
- **Long** – Extended cuff made of nomex fabric and drawstring waistband with Velcro closure.
- **Short** – Basic cuff made of Para-Aramid knitting.

OTHER INFORMATIONS:

- Anatomical glove cut.
- Reflective elements.
- Carabiner for hanging gloves to clothing.
- The gloves complies with EN 659 even after 40 washing cycles at 60 °C.

Measurement type:	Before washing:	After washing:
Abrasion resistance	4	4
Blade cut resistance (palm part)	5	TDM Level E
Tear resistance	4	3
Puncture resistance	3	3
Burning behaviour	4	4
Convection heat resistance	4	4
Radiant heat resistance	2	2
Contact heat resistance	2	2
Dexterity	5	5

STANDARDS:

- EN 659:2003+A1:2008



SIZE ASSORTMENT:

cm	12,7-15,2	15,2-16,5	16,5 - 19	19 - 21,6	21,6 - 24,2	24,2 - 26,7	26,7 - 29,2	29,2 - 30,4	30,4-32,9
velikost	5 (XXS)	6 (XS)	7 (S)	8 (M)	9 (L)	10 (XL)	11 (2XL)	12 (3XL)	13 (4XL)

CARE & MAINTENANCE:

Choose a more ecological short washing program at 40 °C. Wash at a maximum temperature of 60 °C if you need to disinfect the gloves or they are extremely dirty.



PROCEDURE: Remove coarse dirt after each use. Before washing, fasten the Velcro fasteners and remove the snaps. Use a liquid detergent. Wash on a short programme. **TO MAKE THE GLOVE FIT BETTER:** Shape the glove several times after washing and during drying. Do not dry in direct sunlight or heat sources, do not use a tumble dryer. Store the gloves in a dry environment.

RECOMMENDED USE:

Holík Washing Gel

The washing gel is natural based for leather and textile gloves with high washing efficiency. It reduces bacteria, does not pollute the environment and is fully biodegradable (Eco-Friendly).



Impregnation spray Holík

A highly effective impregnating spray for leather and textiles that protects against moisture, water, oil and dirt while maintaining the breathability of the material. Apply the impregnation in a thin layer on dry product and allow to dry for at least 12 hours.

For more about Washing & Maintenance, visit:

www.holik-international.com > [Technologies](#) > [Care&Maintenance](#)



Co-funded by
the European Union

