

LESLEY PLUS 6510

Versatile glove for technical interventions. This model excels in flexibility, sensitivity and high protection against mechanical risks.

PRODUCT DESCRIPTION

Colour: Lime Green
LESLEY PLUS Evo 6510

UPPER MATERIAL:

- **Back:** Durable elastic fabric, color Lime Green.
- **Palm:** Synthetic leather.

REINFORCEMENT:

- Reinforcement of the most exposed areas in the palm – Kevlar® / PA with FR coating and foam padding.
- Reinforcement between thumb and index finger made of Kevlar® / PA with FR coating covers the side seams, increases the life of the glove thanks to high abrasion resistance.
- Anti-slip reinforcements on the fingertips in the palm.
- Protection of the knuckles on the back of the hand against abrasion and impact – Kevlar®/PA with FR coating and foam padding.
- Finger reinforcement on the back of the hand – synthetic leather.

LINING:

- **Palm:** Para-aramid / PES / Fibreglass knitted lining – high cut resistance.

CUFF:

- **Evo:** Elastic cuff with inner wristband preventing ingress of dirt.

STANDARDS:

- EN 420:2003+A1:2009
- EN 388:2016+A1:2018 – 4 5 4 4 D P
- EN ISO 21420:2020



LESLEY PLUS



LESLEY PLUS 6510

OTHER INFORMATION:

- High resistance to mechanical risks.
- Breathability, sensitivity, flexibility and high strength.
- Comfortable cut.
- Anatomically articulated reinforcements in the palm.
- The wrist part is tightened with an elastic band.
- Reflective element.
- Contrast stitching.
- Plastic ring and textile loop for hanging the glove on the carabiner.



Anatomical palm reinforcements




Knuckle protection on the back



Evo cuff

SIZE ASSORTMENT

 cm	12,7-15,2	15,2-16,5	16,5 - 19	19 - 21,6	21,6 - 24,2	24,2 - 26,7	26,7 - 29,2	29,2 - 30,4	30,4-32,9
size	5 (XXS)	6 (XS)	7 (S)	8 (M)	9 (L)	10 (XL)	11 (2XL)	12 (3XL)	13 (4XL)

CARE & MAINTENANCE:

Choose a more ecological short washing program at 40 °C.



PROCEDURE: Remove coarse dirt after each use. Before washing, fasten the Velcro fasteners and remove the snaps. Use a liquid detergent. Wash on a short programme.

TO MAKE THE GLOVE FIT BETTER: Shape the glove several times after washing and during drying. Do not dry in direct sunlight or heat sources, do not use a tumble dryer. Store the gloves in a dry environment.

RECOMMENDED USE:

Holík Washing Gel

The washing gel is natural based for leather and textile gloves with high washing efficiency. It reduces bacteria, does not pollute the environment and is fully biodegradable (Eco-Friendly).



Impregnation spray Holík

A highly effective impregnating spray for leather and textiles that protects against moisture, water, oil and dirt while maintaining the breathability of the material. Apply the impregnation in a thin layer on dry product and allow to dry for at least 12 hours.

For more about Washing & Maintenance, visit:
www.holik-international.com > Technologies > Care&Maintenance



Co-funded by
the European Union

