

## **PENELOPE PLUS Green** 6517

Technical gloves that are extremely sensitive and flexible thanks to the leather palm. In addition, the special seamless fingertip construction improves the handling of small objects. The leather adapts perfectly to the user's hand after several weeks of use, making this model one of our most sensitive rescue gloves.



PENELOPE PLUS Green

### PRODUCT DESCRIPTION

Colour:

PENELOPE PLUS Green

Li

Lime Green 6517

### **UPPER MATERIAL:**

- Back: Elastic fabric combined with hydrophobic goatskin.
- Palm: Goatskin leather with hydrophobic treatment.
- Mid-finger: Elastic fabric combined with hydrophobic goatskin.

### **REINFORCEMENT:**

- TPR reinforcements protection of back joints and fingers.
- Digital leather reinforcements on fingertips.
- Reinforcement between thumb and index finger in Kevlar®/PA fabric with FR coating overlaps the side seams, increases the life of the glove thanks to high abrasion resistance.

## LINING:

• Palm: Para-Aramid / PES / Fibreglass knitted lining – high cut resistance.

### CUFF:

• Neo: Neoprene cuff with velcro closure.

### **OTHER INFORMATION:**

- · High resistance to mechanical risks.
- Breathability, sensitivity, flexibility and high strength.
- The natural leather makes the glove sensitive and flexible.
- The terry cloth on the dorsal thumb serves to wipe away sweat on the face.
- · Contrast stitching.
- Plastic ring and fabric loop for hanging the glove on a carabiner.

  EN 388

### **STANDARDS**:

• EN 388:2016+A1:2018 3 4 4 3 C

DuPont™ and Kevlar® are trademarks or registered trademarks of E.I. du Pont de Nemours and Company.



# **PENELOPE PLUS Green** 6517



Goatskin leather with hydrophobic treatment



Neo cuff



TPR reinforcements on back joints and fingers

### **SIZE ASSORTMENT:**

cm cm	15,2-16,5	16,5 - 19	19 - 21,6	21,6 - 24,2	24,2 - 26,7	26,7 - 29,2	29,2 - 30,4
size	6 (XS)	7 (S)	8 (M)	9 (L)	10 (XL)	11 (2XL)	12 (3XL)

### **CARE & MAINTENANCE:**

Choose a more ecological short washing program at 40 °C.



**PROCEDURE:** Remove coarse dirt after each use. Before washing, fasten the Velcro fasteners and remove the snaps. Use a liquid detergent. Wash on a short programme.

**TO MAKE THE GLOVE FIT BETTER:** Shape the glove several times after washing and during drying. Do not dry in direct sunlight or heat sources, do not use a tumble dryer. Store the gloves in a dry environment.

### **RECOMMENDED USE:**

### Holík Washing Gel

The washing gel is natural based for leather and textile gloves with high washing efficiency. It reduces bacteria, does not pollute the environment and is fully biodegradable (Eco-Friendly).



### Impregnation spray Holík

A highly effective impregnating spray for leather and textiles that protects against moisture, water, oil and dirt while maintaining the breathability of the material. Apply the impregnation in a thin layer on dry product and allow to dry for at least 12 hours.

For more about Washing & Maintenance, visit: www.holik-international.com > Technologies > Care&Maintenance











Holík International, s.r.o.

Za Dvorem 612, Štípa, 763 14 Zlín Tel.: +420 577 125 500

E-mail: info@holik-international.cz Instagram: holik\_international Facebook: holikinternational Web: www.holik-international.cz

### Holík GmbH

Von-der-Goltz Strasse 24 DE-42329 Wuppertal, DE Tel.: +49 (0) 202 786 6278 Mob.: +49 170 788 8432 E-mail: mail@holik-gmbh.de Web: www.holik-ambh.de

### Holík America, LLC

532 N Regional Rd, Ste A Greensboro, NC 27409, USA Cell: +1 631-636-9212 Office: +1 336-907-8001

E-mail: kolar@holik-international.com
Web: www.holik-america.com

